



Studio Isolation Filter



User Manual

Thank you for choosing H&A product! Our goal is to make your professional life easier and to maximize your effectiveness.

Before using the product, please make sure that all the components are present in the package:

- ▶ H&A Studio isolation filter with mount
- ▶ 5/8" Extension stud

Product Features

- ▶ Four layers of acoustic isolation
- ▶ Allows creating clean voice recordings
- ▶ High-density composite fiber
- ▶ Vented back reduces sonic coloration
- ▶ Prevents bounce-back reflections
- ▶ Vertically adjustable microphone mount
- ▶ Strong perforated aluminum frame
- ▶ Integrated clamp for mounting to stands
- ▶ Mount brackets, lock screws, 5/8" mic extension

The filter features a semi-circular anodized aluminum perforated frame that is lined with high-density composite fiber. For mounting on stands, it features a universal two-piece clamp with a swivel capability.

Instructions

1. Before attaching your microphone, mount this isolation filter to a tripod or stable stand using the clamping bracket on the back. Tighten it and make sure your assembly is stable.
2. Then attach a microphone to the L-shaped bracket using the 5/8" extension adapter.
3. Adjust the height as needed for optimal performance.

Specifications

Stand Mount	Universal clamping mount
Microphone Mount	5/8"-27 male
Construction	Anodized aluminum frame High-density composite filter
Dimensions	17.25 x 13.75 x 10.5" / 43.8 x 34.9 x 26.7 cm
Weight	8.3 lb / 3.75 kg

H&A Limited 1-Year USA Warranty

We are excited to have you as a customer and hope that our product serves you well for years to come!

H&A warrants to the original purchaser that your H&A product shall be free from defects in material and workmanship for the period of one (1) year from the date of purchase (or delivery as may be required in certain jurisdictions), or thirty (30) days after replacement, whichever comes later.

H&A's entire liability and your exclusive remedy for any breach of warranty shall be, at H&A's option, to repair or replace the hardware, provided that the hardware is returned to the point of purchase or such other place as H&A may direct with a copy of the sales receipt or dated itemized receipt. H&A may, at its option, replace your product, offer to provide a functionally equivalent product, or repair any product with new, refurbished or used parts as long as such parts are in compliance with the product's technical specifications. Any replacement hardware product will be warranted for the remainder of the original warranty period or thirty (30) days, whichever is longer, or for any additional period of time that may be applicable in your jurisdiction. If the product has been discontinued, the warranty provider reserves the right to replace it with a model of equivalent quality and function.

This warranty does not cover problems or damage resulting from accident, abuse, misapplication, or any unauthorized repair, modification or disassembly, improper operation or maintenance, normal wear and tear, or usage not in accordance with product instructions or connection to improper voltage supply, use of consumables, such as replacement batteries, not supplied by H&A, except where such restriction is prohibited by applicable law.

Except where prohibited by applicable law, this warranty is nontransferable and is limited to the original purchaser and the country in which the product was purchased. This warranty gives you specific legal rights, and you may also have other rights, including a longer warranty duration that may vary under local laws. To start a warranty claim contact the H&A Customer Service Department to obtain a return merchandise authorization ("RMA") number, and return the defective product to H&A, along with the RMA number and proof of purchase.

Question About Our Product Line? Need Product Support?

We are proud of our products and celebrate our customers. We are with you, from product selection to everyday use. Be secure with your purchase and reach us as you need.

Email us: brands@adorama.com

Call us: 212-647-9300

Our address: Adorama Brands, 42 West 18th Street, New York, NY 10011

You can always contact us at BRANDS@ADORAMA.COM for personal technical support. Our web site contains a wide range of Support and FAQ pages with valuable technical assistance.

H&A is a registered trademark of ADORAMA CAMERA.

© 2019 Adorama Inc. All Rights Reserved.

The background is a solid dark blue color. It features three sets of concentric, light-colored circular lines. One set is in the top right corner, another in the bottom left corner, and a third in the bottom right corner. The lines are thin and closely spaced, creating a ripple effect.

HASIF

ADORAMA INC., NEW YORK, NY
www.adorama.com/ourbrands